

Blanking Caps/Socks/Bins

- BFM® blanking caps can be used to prevent contamination during clean down or change-over. They protect products and prevent dust emission into the factory.
- Sifter oversize collection socks or bins are another ideal application for the BFM® concept.
- Transparent for monitoring fill level and reject consistency, socks can be lined with plastic bags for a fast, hygienic solution to disposing of sifter waste.
- Available up to 650mm (25½") diameters.

સ ાભા શ્રેમસાદા સ્ત્રકદ	WE WELL A	

Blanking Sock or Bin

Physical Properties			
Gloss/Gloss			
90			
0.9 mm / 1/32 inch			
-25 to 110°C			
-13 to 230°F			
120°C / 248°F			
0			
Up to 650mm / 25½"			
1,000mm / 39½"			



Blanking Cap

Seeflex 040E material complies with the following regulations:

FDA CFR 177.1680. & 177.2600.